

TIDA-00998 REV E2 Bill of Materials

Item #	Designator	Quantity	Value	PartNumber	Manufacturer	Description	PackageReference	Fitted
1	IPCB	1		TIDA-00998	Any	Printed Circuit Board		Fitted
2	C2, C6	2	4.7uF	0603ZD475KAT2A	AVX	CAP, CERM, 4.7 uF, 10 V, +/- 10%, X5R, 0603	0603	Fitted
3	C3, C4, C7, C10, C16, C17, C19, C20	8	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603	Fitted
4	C5	1	0.01uF	C0603C103J5RACTU	Kemet	CAP, CERM, 0.01 uF, 50 V, +/- 5%, X7R, 0603	0603	Fitted
5	C8, C9	2	100uF	C1210C107M8PACTU	Würth Elektronik	CAP, CERM, 100 uF, 10 V, +/- 20%, X5R, 1210	1210	Fitted
6	C11	1	1uF	C0603C105K8PACTU	Kemet	CAP, CERM, 1 uF, 10 V, +/- 10%, X5R, 0603	0603	Fitted
7	C12, C13	2	2.2uF	GRM219R61E225KA12D	MuRata	CAP, CERM, 2.2 uF, 25 V, +/- 10%, X5R, 0805	0805	Fitted
8	C14, C15	2	0.47uF	C0603C474K8PACTU	Kemet	CAP, CERM, 0.47 uF, 10 V, +/- 10%, X5R, 0603	0603	Fitted
9	D2	1	75V	1N4448WX-TP	Micro Commercial Components	Diode, Switching, 75 V, 0.25 A, SOD-323	SOD-323	Fitted
10	D3, D7, D13	3	Red	HSMZ-A400-V30M1	Avago	LED, Red, SMD	3.2x2.8mm	Fitted
11	D4, D10, D16	3	Yellow	VAOL-S2WR4	Visual Communications Company	LED, Yellow, SMD	3.1x2.7mm	Fitted
12	D5, D6, D8, D9, D11, D12, D14, D15, D17, D18	10	Red	VLMR334BACB-GS08	Vishay-Semiconductor	LED, Red, SMD	3x2.8mm	Fitted
13	D19	1	Red	LNJ8L6C18RA	Panasonic	LED, Red, SMD	3.3x3.1mm	Fitted
14	FID4, FID5, FID6	3	N/A	N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial	Fitted
15	H1	1		IML-0669	MuRata	Lens, Ceiling Mount, TH	D12xH8.508mm	Fitted
16	J1, J4, J5	3		OSTVN02A150	On-Shore Technology	Terminal Block, 2.54mm, 2x1, Brass, TH	Terminal Block, 2.54mm, 2-pole, Brass, TH	Fitted
17	J2	1		PEC03SAAN	Sullins Connector Solutions	Header, 100mil, 3x1, Tin, TH	Header, 3 PIN, 100mil, Tin	Fitted
18	J3, J6	2		61300621121	Würth Elektronik	Header, 2.54mm, 3x2, Gold, TH	Header, 2.54mm, 3x2, TH	Fitted
19	J7	1		61300211121	Würth Elektronik	Header, 2.54 mm, 2x1, Gold, TH	Header, 2.54mm, 2x1, TH	Fitted
20	L1	1	10uH	VLF302515MT-100M	TDK	Inductor, Shielded, Ferrite, 10 uH, 0.71 A, 0.152 ohm, SMD	IND_3x1.5x3mm	Fitted
21	L2	1	10uH	VLF504012MT-100M	TDK	Inductor, Shielded, Ferrite, 10 uH, 1.3 A, 0.19 ohm, SMD	IND_5x1.2x4mm	Fitted
22	LBL1	1		THT-14-423-10	Brady	Thermal Transfer Printable Labels, 0.650" W x 0.200" H - 10,000 per roll	PCB Label 0.650"H x 0.200"W	Fitted
23	Q1, Q2, Q3, Q4	4	-20V	SI1317DL-T1-GE3	Vishay-Siliconix	MOSFET, P-CH, -20 V, -1.4 A, SOT-323	SOT-323	Fitted
24	R1, R3, R6, R7, R10, R18, R20, R21, R22, R27, R30, R31, R32, R34	14	0	RC0603JR-070RL	Yageo America	RES, 0, 5%, 0.1 W, 0603	0603	Fitted
25	R4	1	3.48Meg	CRCW06033M48FKEA	Vishay-Dale	RES, 3.48 M, 1%, 0.1 W, 0603	0603	Fitted
26	R5	1	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603	Fitted
27	R8	1	5.49Meg	CRCW06035M49FKEA	Vishay-Dale	RES, 5.49 M, 1%, 0.1 W, 0603	0603	Fitted
28	R9	1	7.32Meg	CRCW06037M32FKEA	Vishay-Dale	RES, 7.32 M, 1%, 0.1 W, 0603	0603	Fitted
29	R11	1	499	CRCW0603499RFKEA	Vishay-Dale	RES, 499, 1%, 0.1 W, 0603	0603	Fitted
30	R12	1	4.32Meg	CRCW06034M32FKEA	Vishay-Dale	RES, 4.32 M, 1%, 0.1 W, 0603	0603	Fitted
31	R13	1	7.50Meg	CRCW06037M50FKEA	Vishay-Dale	RES, 7.50 M, 1%, 0.1 W, 0603	0603	Fitted
32	R14	1	1.18Meg	CRCW06031M18FKEA	Vishay-Dale	RES, 1.18 M, 1%, 0.1 W, 0603	0603	Fitted
33	R15, R16, R17, R23, R24	5	10.0k	CRCW060310K0FKEA	Vishay-Dale	RES, 10.0 k, 1%, 0.1 W, 0603	0603	Fitted
34	R19	1	8.06k	CRCW06038K06FKEA	Vishay-Dale	RES, 8.06 k, 1%, 0.1 W, 0603	0603	Fitted
35	R28, R29	2	200k	RC0603FR-07200KL	Yageo America	RES, 200 k, 1%, 0.1 W, 0603	0603	Fitted
36	U1	1		BQ25505RGRR	Texas Instruments	Ultra Low Power Boost Converter with Battery Management for Energy Harvester Applications, RGR0020A (VQFN-20)	RGR0020A	Fitted
37	U2	1		TPS2113APWR	Texas Instruments	AUTOSWITCHING POWER MUX, PW0008A (TSSOP-8)	PW0008A	Fitted
38	U3	1		LP55231SQX/NOPB	Texas Instruments	LP55231 Programmable 9-Output LED Driver, RTW0024A (WQFN-24)	RTW0024A	Fitted
39	U4	1		LM3509SD/NOPB	Texas Instruments	High Efficiency Boost for White LED's and/or OLED Displays with Dual Current Sinks and IC Compatible Brightness Control, 10-pin LLP, Pb-Free	SDA10A	Fitted
40	U5	1		OPT3001DNPR	Texas Instruments	Ambient Light Sensor, DNP0006A (USON-6)	DNP0006A	Fitted
41	U7	1		PCA9306DCTR	Texas Instruments	Dual Bi-Directional I2C-Bus and SMBus Voltage Level-Translator, 0 to 5.5 V, -40 to 85 degC, 8-pin SM8 (DCT), Green (RoHS & no Sb/Br)	DCT0008A	Fitted
42	BT1	0		TL-4934/P	Tadiran Batteries	Battery 3.6V, TH	D32.9mm	Not Fitted
43	C1	0	1000000uF	DB-5R5D105T	Elna	CAP, Electric Double Layer, 1F, 5.5 V, +80/-20%, 30 ohm, TH	D21.5xL8mm	Not Fitted
44	C18	0	0.1uF	06033C104JAT2A	AVX	CAP, CERM, 0.1 uF, 25 V, +/- 5%, X7R, 0603	0603	Not Fitted
45	D1	0	5V	1SS315TPH3F	Toshiba	Diode, Schottky, 5 V, 0.03 A, SOD-323	SOD-323	Not Fitted
46	FID1, FID2, FID3	0	N/A	N/A	N/A	Fiducial mark. There is nothing to buy or mount.	Fiducial	Not Fitted
47	R2	0	100k	CRCW0603100KFKEA	Vishay-Dale	RES, 100 k, 1%, 0.1 W, 0603	0603	Not Fitted
48	R25	0	1.80Meg	CRCW06031M80FKEA	Vishay-Dale	RES, 1.80 M, 1%, 0.1 W, AEC-Q200 Grade 0, 0603	0603	Not Fitted
49	R26	0	1.00Meg	CRCW06031M00FKEA	Vishay-Dale	RES, 1.00 M, 1%, 0.1 W, 0603	0603	Not Fitted
50	R33	0	52.3k	CRCW060352K3FKEA	Vishay-Dale	RES, 52.3 k, 1%, 0.1 W, 0603	0603	Not Fitted
51	R35	0	0	RC0603JR-070RL	Yageo America	RES, 0, 5%, 0.1 W, 0603	0603	Not Fitted
52	U6	0		TLV3011AIDCKR	Texas Instruments	Nanopower, 1.8V, Comparator with Voltage Reference, DCK0006A (SOT-6)	DCK0006A	Not Fitted

## IMPORTANT NOTICE FOR TI DESIGN INFORMATION AND RESOURCES

Texas Instruments Incorporated ("TI") technical, application or other design advice, services or information, including, but not limited to, reference designs and materials relating to evaluation modules, (collectively, "TI Resources") are intended to assist designers who are developing applications that incorporate TI products; by downloading, accessing or using any particular TI Resource in any way, you (individually or, if you are acting on behalf of a company, your company) agree to use it solely for this purpose and subject to the terms of this Notice.

TI's provision of TI Resources does not expand or otherwise alter TI's applicable published warranties or warranty disclaimers for TI products, and no additional obligations or liabilities arise from TI providing such TI Resources. TI reserves the right to make corrections, enhancements, improvements and other changes to its TI Resources.

You understand and agree that you remain responsible for using your independent analysis, evaluation and judgment in designing your applications and that you have full and exclusive responsibility to assure the safety of your applications and compliance of your applications (and of all TI products used in or for your applications) with all applicable regulations, laws and other applicable requirements. You represent that, with respect to your applications, you have all the necessary expertise to create and implement safeguards that (1) anticipate dangerous consequences of failures, (2) monitor failures and their consequences, and (3) lessen the likelihood of failures that might cause harm and take appropriate actions. You agree that prior to using or distributing any applications that include TI products, you will thoroughly test such applications and the functionality of such TI products as used in such applications. TI has not conducted any testing other than that specifically described in the published documentation for a particular TI Resource.

You are authorized to use, copy and modify any individual TI Resource only in connection with the development of applications that include the TI product(s) identified in such TI Resource. NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT OF TI OR ANY THIRD PARTY IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information regarding or referencing third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of TI Resources may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI RESOURCES ARE PROVIDED "AS IS" AND WITH ALL FAULTS. TI DISCLAIMS ALL OTHER WARRANTIES OR REPRESENTATIONS, EXPRESS OR IMPLIED, REGARDING TI RESOURCES OR USE THEREOF, INCLUDING BUT NOT LIMITED TO ACCURACY OR COMPLETENESS, TITLE, ANY EPIDEMIC FAILURE WARRANTY AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS.

TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY YOU AGAINST ANY CLAIM, INCLUDING BUT NOT LIMITED TO ANY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON ANY COMBINATION OF PRODUCTS EVEN IF DESCRIBED IN TI RESOURCES OR OTHERWISE. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, DIRECT, SPECIAL, COLLATERAL, INDIRECT, PUNITIVE, INCIDENTAL, CONSEQUENTIAL OR EXEMPLARY DAMAGES IN CONNECTION WITH OR ARISING OUT OF TI RESOURCES OR USE THEREOF, AND REGARDLESS OF WHETHER TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES.

You agree to fully indemnify TI and its representatives against any damages, costs, losses, and/or liabilities arising out of your non-compliance with the terms and provisions of this Notice.

This Notice applies to TI Resources. Additional terms apply to the use and purchase of certain types of materials, TI products and services. These include; without limitation, TI's standard terms for semiconductor products (<http://www.ti.com/sc/docs/stdterms.htm>), [evaluation modules](#), and [samples](http://www.ti.com/sc/docs/sampterm.htm) (<http://www.ti.com/sc/docs/sampterm.htm>).

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2017, Texas Instruments Incorporated