

Ref/Part name	pcs/unit
C2	1
C3	1
C4	0
C21 C31	2
C41	1
C101 C151 C241 C331 C361 C391 C431	7
C281	1
C321 C551 C561	3
C341 C351	2
C371 C381	2
C372 C382	2
C373	1
C374	0
C392	1
C441 C451	2
FL1	1
J1	1
J2	0
L372 L373 L381	3
L374	0
L375	1
P1 P2	2
P3	0
P5	1
P6	0
R1 R442 R452	0
R21 R31	2
R32	1
R41	1
R281	1
R421	1
R441 R451	2
U1	1
U2	1
X1	1
X2	1
Total number of components to be mounted	47

Description

CAPACITOR, CERAMIC X5R, 2.2uF, 10V, -20%/+20%, -55DEGC/+85DEGC, 0603, SMD
CAPACITORS, CERAMIC, 1uF, 15%, X5R, 10V, 0603, SMD
CAPACITOR, DO NOT MOUNT, 0603, SMD
CAPACITOR, CERAMIC COG/NPO, 47pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD
CAPACITOR, CERAMIC X5R, 4.7uF, 6.3V, -10%/+10%, -55DEGC/+85DEGC, 0603, SMD
CAPACITOR, CERAMIC X7R, 100nF, 6.3V, -10%/+10%, -55DEGC/+125DEGC, 0402, SMD
CAPACITOR, CERAMIC X7R, 1nF, 50V, -10%/+10%, -55DEGC/+125DEGC, 0402, SMD
CAPACITOR, CERAMIC X5R, 1uF, 10V, -10%/+10%, -55DEGC/+85DEGC, 0402, SMD
CAPACITOR, CERAMIC COG/NPO, 12pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD
CAPACITOR, CERAMIC COG/NPO, 18pF, 50V, -55DEGC/+125DEGC, 0402, SMD
CAPACITOR, CERAMIC COG/NPO, 1pF, 50V, -0.1pF/+0.1pF, -55DEGC/+125DEGC, 0402, SMD
CAPACITOR, CERAMIC COG/NPO, 1.2pF, 50V, -0.25pF/ +0.25pF, -55DEGC/+125DEGC, 0402, SMD
CAPACITOR, DO NOT MOUNT, 0402, SMD
CAPACITOR, CERAMIC COG/NPO, 220pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD
CAPACITOR, CERAMIC COG/NPO, 22pF, 50V, -5%/+5%, -55DEGC/+125DEGC, 0402, SMD
FILTER, EMI, 1500@100MHz, -55DEGC/+125DEGC, 0603, SMD
CONNECTOR, USB-B, 5 PINS, PITCH 0.65mm, SMD
CONNECTOR, COAX RF, DO NOT MOUNT
INDUCTOR, CHIP, 2nH, -0.3nH/ +0.3nH, 0.3A, -55DEGC/+125DEGC, 0402, SMD
INDUCTOR, DO NOT MOUNT, 0402, SMD
INDUCTOR, STANDARD, 3.3nH, -0.3nH/+0.3nH, 0.3A, -55DEGC/+125DEGC, 0402, SMD
CONNECTOR, HEADER, FEMALE, STRAIGHT, 2 ROWS, 20 PINS, PITCH 1.27mm, SMD
CONNECTOR, DO NOT MOUNT, SMD
CONNECTOR, HEADER, STRAIGHT, MALE, 4 PINS, 2 ROWS, 2.54mm PITCH, SMD
CONNECTOR, DO NOT MOUNT
RESISTOR, DO NOT MOUNT, 0402, SMD
RESISTOR, THICK FILM, 33, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD
RESISTOR, THICK FILM, 1.5k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD
RESISTOR, THICK FILM, 2, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD
RESISTOR, THICK FILM, 2.2k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD
RESISTOR, THICK FILM, 56k, -1%/+1%, 0.063W, 50V, -55DEGC/+155DEGC, 0402, SMD
RESISTOR, JUMPER, -55DEGC/+155DEGC, 0402, SMD
IC, ANALOG, ARM CORTEX M3 MCU WITH 2.4GHz IEEE 802.15.4 ZigBee, 2V TO 3.6V, -40DEGC/+125 DEGC, VQFN5
IC, ANALOG, ULTRALOW-POWER LINEAR REGULATORS, VIN:3.2.7V TO 10V, VOUT: 3.3V, SOT23-5, SMD
CRYSTAL, OSCILATOR, 32MHz, 10pF, -10PPM/+10PPM, -40DEGC/+85DEGC, SMD
CRYSTAL, OSCILATOR, 32.768kHz, -20PPM/ + 20PPM, -40DEGC/ +85DEGC, 12.5pF, SMD

Manufacturer	Value	Part Number
MURATA	2.2uF	02-01132
MURATA	1uF	02-01389
	DNM	02-01324
MURATA	47pF	02-04366
MURATA	4.7uF	02-02418
MURATA	100nF	02-02323
MURATA	1nF	02-02070
MURATA	1uF	02-02381
MURATA	12pF	02-04168
MURATA	18pF	02-02407
MURATA	1pF	02-04367
MURATA	1.2pF	02-04524
	DNM	02-01321
MURATA	220pF	02-01276
MURATA	22pF	02-04373
MURATA	BLM18HE152SN1	04-00470
Tyco	1981568-1	06-02244
MURATA	2nH	03-06525
	TBD	03-01022
MURATA	3.3nH	03-06501
SAMTEC	SFM-110-02-S-D-A-K-TR	06-02251
GradConn Cable	BB02-HP041-KB3-060B00	06-02190
AMP TYCO ELECTRONICS CORPORATION	826629-2	06-00059
	DNM	01-02475
KOA SPEER	33	01-16853
KOA SPEER	1.5k	01-16854
KOA SPEER	2	01-16855
KOA SPEER	2.2k	01-11503
KOA SPEER	56k	01-16848
KOA SPEER	0	01-01784
TEXAS INSTRUMENTS	CC2538F512RKU	18-27810
TEXAS INSTRUMENTS	TPS76933	18-00550
Epson Toyocom	32MHz	12-00422
Epson Toyocom	32.768kHz	12-00430

MPN	PCB Packag	Rtd Voltage	Min Oper Temp	Max Oper Temp
GRM188R61A225ME34D	0603	10V	-55DEGC	+85DEGC
GRM188R61A105KA61D	0603	10V	-55DEGC	+85DEGC
GRM1555C1H470JA01D	0402	50V	-55DEGC	+125DEGC
GRM188R60J475KE19D	0603	6.3V	-55DEGC	+85DEGC
GRM155R70J104KA01D	0402	6.3V	-55DEGC	+125DEGC
GRM155R71H102KA01D	0402	50V	-55DEGC	+125DEGC
GRM155R61A105KE15D	0402	10V	-55DEGC	+85DEGC
GRM1555C1H120JA01D	0402	50V	-55DEGC	+125DEGC
GRM1555C1H180JA01D	0402	50V	-55DEGC	+125DEGC
GRM1555C1H1R0BA01D	0402	50V	-55DEGC	+125DEGC
GRM1555C1H1R2CA01D	0402	50V	-55DEGC	+125DEGC
GRM1555C1H221JA01D	0402	50V	-55DEGC	+125DEGC
GRM1555C1H220JA01D	0402	50V	-55DEGC	+125DEGC
BLM18HE152SN1D	0603		-55DEGC	+125DEGC
1981568-1			N/A	N/A
LQG15HS2N0S02D	0402		-55DEGC	+125DEGC
LQG15HS3N3S02D	0402		-55DEGC	+125DEGC
SFM-110-02-SM-D-A-K-TR			-55DEGC	+125DEGC
BB02-HP041-KB3-060B00			-40DEGC	+105DEGC
826629-2		750V	-65DEGC	+105DEGC
RK73H1ETTP33R0F	0402	50V	-55DEGC	+155DEGC
RK73H1ETTP1501F	0402	50V	-55DEGC	+155DEGC
RK73H1ETTP2R00F	0402	50V	-55DEGC	+155DEGC
RK73H1ETTP2201F	0402	50V	-55DEGC	+155DEGC
RK73H1ETTP5602F	0402	50V	-55DEGC	+155DEGC
RK73Z1ETTP	0402		-55DEGC	+155DEGC
CC2538F512RKU	VQFN56	2V TO 3.6V	-40DEGC	+125DEGC
TPS76933DBVT	SOT23-5	3.3V	-40DEGC	+125DEGC
FA-128 32MHz 10pF 10PPM	SMD		-40DEGC	+85DEGC
FC-12M 32.768kHz 20ppm			-40DEGC	+85DEGC

IMPORTANT NOTICE FOR TI REFERENCE DESIGNS

Texas Instruments Incorporated ("TI") reference designs are solely intended to assist designers ("Buyers") who are developing systems that incorporate TI semiconductor products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, evaluation and judgment in designing Buyer's systems and products.

TI reference designs have been created using standard laboratory conditions and engineering practices. **TI has not conducted any testing other than that specifically described in the published documentation for a particular reference design.** TI may make corrections, enhancements, improvements and other changes to its reference designs.

Buyers are authorized to use TI reference designs with the TI component(s) identified in each particular reference design and to modify the reference design in the development of their end products. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OR OTHERWISE TO ANY OTHER TI INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN, including but not limited to any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services, or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

TI REFERENCE DESIGNS ARE PROVIDED "AS IS". TI MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE REFERENCE DESIGNS OR USE OF THE REFERENCE DESIGNS, EXPRESS, IMPLIED OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. TI DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO TI REFERENCE DESIGNS OR USE THEREOF. TI SHALL NOT BE LIABLE FOR AND SHALL NOT DEFEND OR INDEMNIFY BUYERS AGAINST ANY THIRD PARTY INFRINGEMENT CLAIM THAT RELATES TO OR IS BASED ON A COMBINATION OF COMPONENTS PROVIDED IN A TI REFERENCE DESIGN. IN NO EVENT SHALL TI BE LIABLE FOR ANY ACTUAL, SPECIAL, INCIDENTAL, CONSEQUENTIAL OR INDIRECT DAMAGES, HOWEVER CAUSED, ON ANY THEORY OF LIABILITY AND WHETHER OR NOT TI HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES, ARISING IN ANY WAY OUT OF TI REFERENCE DESIGNS OR BUYER'S USE OF TI REFERENCE DESIGNS.

TI reserves the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques for TI components are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

Reproduction of significant portions of TI information in TI data books, data sheets or reference designs is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards that anticipate dangerous failures, monitor failures and their consequences, lessen the likelihood of dangerous failures and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in Buyer's safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed an agreement specifically governing such use.

Only those TI components that TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components that have **not** been so designated is solely at Buyer's risk, and Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.